

# Product data sheet

Specifications



## 16AX/20A 1 Gang 1 Way Full-Flat Switch with Ondicator, Silver Satin

E8431-1\_SA

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	ZENcelo
Product Or Component Type	Switch
Load Type	Inductive Fluorescent lamp Incandescent lamp Resistive
Colour Tint	Silver satin
Cover Frame Colour Tint	Silver satin

### Complementary

Device Mounting	Surface Flush
Switch Function	1-way
Rated Current	20 A at 250 V AC 50/60 Hz
Local Signalling	Mechanical indicator (amber)
Number Of Gangs	1 gang
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

### Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	MS IEC 60669-1 SS 227-1 IEC 60669-1 GB 16915.1 EN 60669-1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.001 g

## Contractual warranty

Warranty	18 months
----------	-----------