

Product data sheet

Specifications



16AX/20A 1 Gang 2 Way Full-Flat Switch, Silver Satin

E8431-2_SA

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	ZENcelo
Product Or Component Type	Switch
Load Type	Resistive Fluorescent lamp Inductive Incandescent lamp
Colour Tint	Silver satin
Cover Frame Colour Tint	Silver satin

Complementary

Device Mounting	Surface Flush
Switch Function	2-way
Rated Current	20 A at 250 V AC 50/60 Hz
Local Signalling	Mechanical indicator (amber)
Number Of Gangs	1 gang
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	EN 60669-1 IEC 60669-1 SS 227-1 MS IEC 60669-1 GB 16915.1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.001 g

Contractual warranty

Warranty	18 months
----------	-----------