

Product data sheet

Specifications



32A 1 Gang Full-Flat Double Rocker Switch with Neon, Sliver White

E8431D32_SW

⚠ Discontinued on: Feb 17, 2017

⚠ Discontinued

Main

Range	ZENcelo
Product Or Component Type	Switch
Load Type	Resistive
Colour Tint	Silver satin
Cover Frame Colour Tint	Silver satin

Complementary

Device Mounting	Surface Flush
Rated Current	32 A at 250 V AC 50/60 Hz
Local Signalling	Indicator light, neon (amber)
Number Of Gangs	1 gang
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - Terminals	Brass rod terminals
Embedding Depth	22 mm
Width	87 mm
Height	87 mm
Depth	30.2 mm

Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Standards	IEC 60669-1 BS EN 60669-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.7 cm
Package 1 Length	8.7 cm
Package 1 Weight	161.72 g

Contractual warranty

Warranty	18 months
----------	-----------