



## Main

Range	ZENcelo
Product or component type	TV/FM/SAT socket
TV socket type	TV
TV connector	F connectors
Additional information	Slave
Colour tint	Wine gold

## Complementary

Device mounting	Flush Surface
Number of gangs	1 gang
Material	Polycarbonate cover Polycarbonate grid plate Polycarbonate surround
Bandwidth	5...1000 Hz
Insertion loss	< 1 dB
Connections - terminals	Clamps terminal F connectors Clamps terminal saddle terminal Pillar terminal without pressure plate inner
Width	87 mm
Height	87 mm
Depth	33.4 mm

## Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	BS 3041

## Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant <a href="#">Will not be compliant</a>
------------------------	--