

Product data sheet

Specifications



2 Gang Data Outlet Category 6 on Shuttered Wallplate, Silver Satin

E8432RJS-6_SA

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	ZENcelo
Product Or Component Type	Data socket
Socket Additional Information	Shuttered
Colour Tint	Silver satin

Complementary

Rated Current	1.5 A
Communication Network Category	Data: 6
Insulation Resistance	>= 200 mOhm
Contact Resistance	1 μOhm
Number Of Gangs	2 gangs
Minimum Return Loss	23 dB
Awg Gauge	AWG 26...AWG 22 (4 twisted pair cables)
Contacts Material	Housing: PC Contact: phosphor bronze with gold plating IDC contact: phosphor bronze with nickel plating
Material	Polycarbonate: plastic part
Device Mounting	Surface Flush
Width	87 mm
Height	87 mm
Depth	36 mm

Environment

Dielectric Strength	1000 V for 60 s at 60 Hz
Ambient Air Temperature For Operation	1...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Standards	ASTMD4566-98 TIA/EIA-568-B.2-1

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.001 g

Contractual warranty

Warranty	18 months
----------	-----------