

# Product data sheet

Specifications



## 2 Gang Telephone + Data Outlet Category 5e on Shuttered Wallplate, Silver Satin

E8432TDRJS-5\_SA

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

Range	ZENcelo
Product Or Component Type	Telephone + data socket
Socket Additional Information	Shuttered
Colour Tint	Silver satin

### Complementary

Communication Network Category	Voice: 3 Data: 5e
Insulation Resistance	>= 200 mOhm
Number Of Gangs	2 gangs
Contacts Material	Contact: phosphor bronze with gold plating IDC contact: phosphor bronze with nickel plating
Material	Polycarbonate plastic part
Device Mounting	Surface Flush
Width	87 mm
Height	87 mm
Depth	36 mm
Embedding Depth	30.2 mm

### Environment

Awg Gauge	AWG 34...AWG 23 (4 twisted pair cables)
Dielectric Strength	1000 V for 60 s at 60 Hz
Ambient Air Temperature For Operation	0...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Standards	ASTMD4566-98 TIA/EIA-568-B.2-1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.001 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------