

Product data sheet

Characteristics

E8432TDRJS-5_SA

2 Gang Telephone + Data Outlet Category 5e on Shuttered Wallplate, Silver Satin



Main

Range	ZENcelo
Product or component type	Telephone + data socket
Socket additional information	Shuttered
Colour tint	Silver satin

Complementary

Communication network category	Voice : 3 Data : 5e
Insulation resistance	>= 200 MOhm
Number of gangs	2 gangs
Return loss	>= 23 dB
Contacts material	Phosphor bronze with gold plating for contact Phosphor bronze with nickel plating for IDC contact
Material	Polycarbonate plastic part
Device mounting	Flush Surface
Width	87 mm
Height	87 mm
Depth	36 mm
Embedding depth	30.2 mm

Environment

AWG gauge	AWG 26...AWG 22 for 4 twisted pair cables
Dielectric strength	1000 V for 60 s at 60 Hz
Ambient air temperature for operation	0...35 °C
Relative humidity	0...95 %
Environmental characteristic	No UV resistant
Standards	TIA/EIA-568-B.2-1 ASTMD4566-98

Contractual warranty

Warranty period	18 months
-----------------	-----------