

Product data sheet

Specifications



2 Gang Telephone + Data Outlet Category 6 on Shuttered Wallplate, Silver Satin

E8432TDRJS-6_SA

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

Range	ZENcelo
Product Or Component Type	Telephone + data socket
Socket Additional Information	Shuttered
Colour Tint	Silver satin

Complementary

Communication Network Category	Voice: 3 Data: 6
Insulation Resistance	>= 200 mOhm
Number Of Gangs	2 gangs
Contacts Material	Contact: phosphor bronze with gold plating IDC contact: phosphor bronze with nickel plating
Material	Polycarbonate plastic part
Device Mounting	Flush Surface
Width	87 mm
Height	87 mm
Depth	36 mm
Embedding Depth	30.2 mm

Environment

Awg Gauge	AWG 34...AWG 23 (4 twisted pair cables)
Dielectric Strength	1000 V for 60 s at 60 Hz
Ambient Air Temperature For Operation	0...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Standards	ASTMD4566-98 TIA/EIA-568-B.2-1

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.001 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------