



Main

Product or component type	USB charger
Device presentation	Mechanism
Colour tint	Silver bronze
Number of terminals	2 screw terminals

Complementary

Device mounting	Flush
Surface finish	Glossy
Surface treatment	Untreated
Number of modules	2 modules 46 x 36.7 x 21.7 mm
Fixing mode	Screw
[Ue] rated operational voltage	100/240 V, supply: AC frequency 50/60 Hz
Integrated connection type	USB port 2.5 V DC 2.1 A
Material	PA (polyamide) 6, for housing Silicone rubber, for cover PC (polycarbonate), for grid plate
Shape of screw head	Cross
Clamping connection capacity	2.5 mm ² rigid 2.5 mm ² stranded 2.5 mm ² flexible 1.5 mm ² stranded 1.5 mm ² flexible 1.5 mm ² rigid
Wire stripping length	6 mm
Product compatibility	Apple Samsung HW XiaoMi HTC Major smart phone and tablet Power bank
Height	87 mm
Width	87 mm
Depth	39 mm
Embedding depth	29.3 mm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product weight	0.1113 kg
----------------	-----------

Environment

Ambient air temperature for storage	-5...60 °C
Relative humidity	10...90 %
Product certifications	CCC IEC
IP degree of protection	IP20
Environmental characteristic	Alcohol Liquid soap
Environmental health and issues	Halogen free
