

Product data sheet

Specifications



16AX 3 Gang 1 Way Full-Flat Switch with Ondicator, Silver Bronze

E8433-1CS_SZ

⚠ Discontinued on: Dec 21, 2012

⚠ Discontinued

Main

Range	ZENcelo
Product Or Component Type	Switch
Load Type	Fluorescent lamp Inductive Resistive Incandescent lamp
Colour Tint	Silver bronze
Cover Frame Colour Tint	Silver bronze

Complementary

Device Mounting	Flush Surface
Switch Function	1-way
Rated Current	16 AX at 250 V AC 50/60 Hz
Local Signalling	Mechanical indicator (amber)
Number Of Gangs	3 gangs
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Standards	MS IEC 60669-1 GB 16915.1 SS 227-1 IEC 60669-1 EN 60669-1

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months