

# Product data sheet

Specifications



## 16AX 3 Gang 1 Way Full-Flat Switch with Ondicator, White

E8433-1CS\_WE

⚠ Discontinued on: Dec 21, 2012

⚠ Discontinued

### Main

Range	ZENcelo
Product Or Component Type	Switch
Load Type	Incandescent lamp Resistive Inductive Fluorescent lamp
Colour Tint	White
Cover Frame Colour Tint	White

### Complementary

Device Mounting	Flush Surface
Switch Function	1-way
Rated Current	16 AX at 250 V AC 50/60 Hz
Local Signalling	Mechanical indicator (amber)
Number Of Gangs	3 gangs
Material	Polycarbonate + GF 20 %: grid plate Polycarbonate: base Polycarbonate: cover Polycarbonate: surround
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

### Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Standards	SS 227-1 IEC 60669-1 MS IEC 60669-1 GB 16915.1 EN 60669-1

### Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months