



Main

Range	ZENcelo
Product or component type	Switch
Switch function	2-way
Number of gangs	3 gangs

Complementary

Device mounting	Flush Surface
Type of packing	Blister
Rated current	20 A (250 V AC, 50/60 Hz)
Local signalling	Amber mechanical indicator
Material	Cover : polycarbonate Surround : polycarbonate Base : polycarbonate Grid plate : polycarbonate + GF 20 %
Load type	Fluorescent lamp Incandescent lamp Inductive Resistive
Cover frame colour tint	Silver satin
Connections - terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	31 mm

Environment

Ambient air temperature for operation	-5...35 °C
Relative humidity	0...95 %
Environmental characteristic	Dust resistant
Operating altitude	2000 m
Standards	EN 60669-1 GB 16915.1 IEC 60669-1 MS IEC 60669-1

