

Product data sheet

Specifications



10A 1 Gang 2 Universal Pin + 3 Flat Pin Socket with Shutter, Silver Satin

E84426-10US_SA

Main

Product Or Component Type	Power socket-outlet
Socket Additional Information	Shuttered
Outlet Poles Configuration	2P + E China 2P universal
Load Type	Resistive
Cover Frame Colour Tint	Silver satin
Cover Plate Colour Tint	Grey

Complementary

Device Mounting	Flush Surface
Rated Current	10 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Polycarbonate grid plate Polycarbonate surround Brass contact plate Phosphor bronze contact plate
Connections - Terminals	Clamps terminal
Embedding Depth	17.8 mm
Width	87 mm
Height	87 mm
Depth	27 mm

Environment

Ambient Air Temperature For Operation	-5...35 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Weight	0.001 g

Contractual warranty

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Warranty

18 months