

# Product data sheet

Specifications



## 16A 250V 1 Gang 3 Pin Universal Socket with Shutter, Silver Satin

E84426UEST\_SA

⚠ Discontinued on: Jul 20, 2017

⚠ End-of-service on: Dec 15, 2017

⚠ Discontinued

### Main

Product Or Component Type	Power socket-outlet
Outlet Poles Configuration	2P + E American
Load Type	Resistive
Cover Frame Colour Tint	Silver satin
Cover Plate Colour Tint	Grey

### Complementary

Device Mounting	Surface Flush
Rated Current	16 A at 250 V AC 50 Hz
Number Of Gangs	1 gang
Material	Brass metal parts Nylon + GF shutter Steel metal parts PC base PC cover
Connections - Terminals	Brass rod terminals
Width	87 mm
Height	87 mm
Depth	29 mm

### Environment

Ambient Air Temperature For Operation	-5...40 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	IEC 60884-1
Standards	IEC 60884-1

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	3 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Width	8.8 cm
Package 1 Length	8.8 cm
Package 1 Weight	79 g

## Contractual warranty

Warranty	18 months
----------	-----------