



### Main

Product or component type	Power socket-outlet
Outlet poles configuration	2P + E
Load type	Resistive
Cover frame colour tint	Silver satin
Cover plate colour tint	Grey

### Complementary

Device mounting	Flush Surface
Local signalling	Indicator light neon amber
Rated current	13 A 250 V AC 50 Hz
Number of gangs	2 gangs
Material	Brass contact Phosphor bronze contact Polycarbonate base Polycarbonate grid plate Polycarbonate surround
Connections - terminals	Folded terminal
Width	147 mm
Height	87 mm
Depth	8 mm

### Environment

Ambient air temperature for operation	-5...40 °C
Relative humidity	0...95 %
Environmental characteristic	UV resistant indoor use
Operating altitude	2000 m
Standards	BS 1363-2 MS 589 SS 145
Standards	SS 145 BS 1363-2 MS 589

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

---

Warranty period	18 months
-----------------	-----------

---