

# Product data sheet

Specifications



## 16A 250V Twin Gang Schuko Socket, White

E84T426-16S\_WE

⚠ Discontinued on: Dec 1, 2020

⚠ Discontinued

### Main

Product Or Component Type	Power socket-outlet
Socket Additional Information	Shuttered
Outlet Poles Configuration	2P + E
Load Type	Resistive
Colour Tint	White
Cover Frame Colour Tint	White

### Complementary

Device Mounting	Surface Flush
Rated Current	16 A at 250 V AC 50 Hz
Number Of Gangs	2 gangs
Material	Polycarbonate base Polycarbonate grid plate Polycarbonate surround Polycarbonate cover Steel terminals
Connections - Terminals	Clamps terminal
Embedding Depth	29 mm
Width	147 mm
Height	87 mm
Depth	40 mm

### Environment

Ambient Air Temperature For Operation	-5...25 °C
Relative Humidity	0...95 %
Environmental Characteristic	No UV resistant
Operating Altitude	2000 m
Standards	IEC 60884-1
Standards	IEC 60884-1

### Contractual warranty

Warranty	18 months
----------	-----------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

