



Main

Range of product	Easergy T300
Product compatibility	PS25
Device short name	BAT5.5AH
Output voltage	12 V DC
Battery type	VRLA
Internal resistance	138 mOhm conforming to IEC 60896-2
Short-circuit current	93 A conforming to IEC 60896-2

Complementary

Battery capacity	5.5 Ah
Height	98.4 mm
Width	65.5 mm
Depth	152 mm
Product weight	2.5 kg
Connector type	Faston
Self-discharge rate	4 %, 1 month at 20 °C
Battery life	12 yr at 20 °C conforming to EUROBAT

Environment

Ambient air temperature for operation	-20...40 °C
---------------------------------------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications