



### Main

Range of product	Easergy T300
Device short name	HU250-EB
Product or component type	Empty modem box

### Environment

IK degree of protection	IK07 conforming to IEC 62262
Relative humidity	95 % conforming to IEC 60068-2-30
Ambient air temperature for operation	-40...85 °C
Ambient air temperature for storage	-40...85 °C
Fire resistance	850 °C
Operating altitude	3000 m
Product certifications	CE
Height	30 mm
Width	115 mm
Depth	133 mm
Product weight	0.105 kg

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1635 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>