

Product data sheet

Specifications



Mureva BOX - junction box - 10 grommets Ø32 + 10xØ40 - 325x175x120 mm

ENN05019

Main

Product Range	Mureva BOX
Product Type	Junction box
Quantity Per Package	1 piece

Complementary

Mounting	Surface
Cable Entry	Grommets
Fixing Mode	Screw-fixed: cover
Inner Dimensions	325 x 175 x 120 mm
Number Of Cable Entries	10 diameter: 32 mm 10 diameter: 40 mm
Material	PP (polypropylene): cover SBS (styrene butadiene styrene): grommet
Electrical Insulation Class	Class II conforming to IEC 536
Height	130 mm
Width	345 mm
Depth	300 mm
Net Weight	1.28 kg

Environment

Operating Temperature	-25...40 °C
Ip-Class	IP55 conforming to IEC 60529
Ik-Class	IK07 conforming to EN 50102
Glow Wire Temperature	750 °C
Standards	EN 60670 CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	13 cm
Package 1 Width	30 cm
Package 1 Length	35 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	1.403 kg
Unit Type Of Package 2	CAR
Number Of Units In Package 2	5
Package 2 Height	40 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	8.014 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	60
Package 3 Height	136 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	104 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations