

# Product data sheet

Specifications



## Mureva BOX - junction box - knock-out 4xM16/20 - 65x65x45 mm

ENN05082

### Main

Product Range	Mureva BOX
Product Type	Junction box
Quantity Per Package	5 pieces

### Complementary

Mounting	Surface
Cable Entry	Knock-out
Fixing Mode	Clip-on: cover
Inner Dimensions	65 x 65 x 45 mm
Number Of Cable Entries	4 x M16/20
Material	ABS (acrylonitrile butadiene-styrene): body PP (polypropylene): cover
Electrical Insulation Class	Class II conforming to IEC 536
Height	45 mm
Width	74 mm
Depth	74 mm
Net Weight	0.052 kg

### Environment

Operating Temperature	-25...40 °C
Ip-Class	IP55 conforming to IEC 60529
Ik-Class	IK07 conforming to EN 50102
Glow Wire Temperature	650 °C
Standards	EN 60670 CE

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.5 cm
Package 1 Width	1.5 cm
Package 1 Length	5.2 cm
Package 1 Weight	52 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations