

Product data sheet

Specifications



Mureva BOX - junction box - 4 grommets Ø20 - 60x60x40 mm

ENN05121

Main

Product Range	Mureva BOX
Product Type	Junction box
Quantity Per Package	1 piece

Complementary

Mounting	Surface
Cable Entry	Grommets
Fixing Mode	Clip-on: cover
Inner Dimensions	60 x 60 x 40 mm
Number Of Cable Entries	4 diameter: 20 mm
Material	ABS (acrylonitrile butadiene-styrene): body PP (polypropylene): cover SBS (styrene butadiene styrene): grommet
Electrical Insulation Class	Class II conforming to IEC 536
Height	50 mm
Width	72 mm
Depth	72 mm
Net Weight	0.048 kg

Environment

Operating Temperature	-25...40 °C
Ip-Class	IP55 conforming to IEC 60529
Ik-Class	IK07 conforming to EN 50102
Glow Wire Temperature	650 °C
Standards	EN 60670
Product Certifications	CE

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4 cm
Package 1 Width	6 cm
Package 1 Length	6 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	48 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	200
Package 2 Height	28 cm
Package 2 Width	40 cm
Package 2 Length	52.5 cm
Package 2 Weight	9.8 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	2400
Package 3 Height	98 cm
Package 3 Width	80 cm
Package 3 Length	120 cm
Package 3 Weight	129.4 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations