

Product data sheet

Specifications



Mureva BOX - security junction box - 10 grommets Ø25 - 150x105x80 mm

ENN05167

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

Main

| | |
|----------------------|------------------------------------|
| Product Range | Mureva BOX |
| Product Type | Junction box for security circuits |
| Quantity Per Package | 1 piece |

Complementary

| | |
|-----------------------------|--|
| Mounting | Surface |
| Cable Entry | Grommets |
| Fixing Mode | Screw-fixed: cover |
| Inner Dimensions | 150 x 105 x 80 mm |
| Number Of Cable Entries | 10 diameter: 25 mm |
| Material | PP (polypropylene): body and cover SBS (styrene butadiene styrene): grommet |
| Electrical Insulation Class | Class II conforming to IEC 536 |
| Height | 87 mm |
| Width | 171 mm |
| Depth | 128 mm |
| Net Weight | 0.26 kg |

Environment

| | |
|------------------------------|------------------------------|
| Operating Temperature | -25...40 °C |
| Ip-Class | IP55 conforming to IEC 60529 |
| Ik-Class | IK07 conforming to EN 50102 |
| Glow Wire Temperature | 960 °C |
| Standards | EN 60670 CE |
| Environmental Characteristic | Slightly halogenated |

Packing Units

| | |
|------------------------------|-------|
| Unit Type Of Package 1 | PCE |
| Number Of Units In Package 1 | 1 |
| Package 1 Height | 9 cm |
| Package 1 Width | 13 cm |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

| | |
|------------------------------|-----------|
| Package 1 Length | 17 cm |
| Package 1 Weight | 258 g |
| Unit Type Of Package 2 | CAR |
| Number Of Units In Package 2 | 36 |
| Package 2 Height | 40 cm |
| Package 2 Width | 40 cm |
| Package 2 Length | 60 cm |
| Package 2 Weight | 10.184 kg |
| Unit Type Of Package 3 | PAM |
| Number Of Units In Package 3 | 900 |
| Package 3 Height | 215 cm |
| Package 3 Width | 100 cm |
| Package 3 Length | 120 cm |
| Package 3 Weight | 313.5 kg |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

| | | |
|---|----------------------------|-----|
| ✓ | Reach Free Of Svhc | |
| ✓ | Toxic Heavy Metal Free | |
| ✓ | Mercury Free | |
| ✓ | Rohs Exemption Information | Yes |

Certifications & Standards

| | |
|--------------------------|---|
| Reach Regulation | REACH Declaration |
| Eu Rohs Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| China Rohs Regulation | China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile |
| Circularity Profile | No need of specific recycling operations |