

# Product data sheet

Specifications



## Mureva TUBE - elbow - white - Ø16 mm

ENN42916

⚠ Discontinued on: Oct 10, 2018

⚠ End-of-service on: Dec 5, 2018

⚠ Discontinued

### Main

Range Of Product	Mureva
Product Or Component Type	Elbow
Colour	White
Quantity Per Package	50 pieces

### Complementary

Accessory / Separate Part Category	Installation accessory
Condition Of Use	Indoor/outdoor
Material	PVC (polyvinyl chloride)
Crush Resistance	750 N/m
Nominal Cross Section	43 mm²
Internal Diameter	12.8 mm
External Diameter	16 mm
Net Weight	0.016 kg

### Environment

Operating Temperature	-5...60 °C
Quality Labels	NF
Standards	EN 61386-21 : 2004 EN 50086-2-1
Environmental Characteristic	Non-flame propagating
Ip-Class	IP40
Ik-Class	IK07

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	24 cm
Package 1 Width	16.5 cm
Package 1 Length	13 cm
Package 1 Weight	0.016 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

# Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Certifications & Standards

**Eu Rohs Directive**

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)