

Product data sheet

Specifications

Mureva FIX - instacable for Ø16-32 mm conduits



ENN47930

Main

Range Of Product	Mureva
Product Or Component Type	Conduit clip
Colour	Grey (RAL 7035)
Quantity Per Package	100 pieces

Complementary

Accessory / Separate Part Category	Installation accessory
Condition Of Use	Indoor
Tube Diameter	16...32 mm
Material	PA (polyamide) 6/6
Fixing Mode	By Murafix plug By screw
Net Weight	0.003 kg

Environment

Operating Temperature	-40...85 °C
-----------------------	-------------

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.500 cm
Package 1 Width	15.500 cm
Package 1 Length	0.230 cm
Package 1 Weight	3.000 g
Unit Type Of Package 2	CAR
Number Of Units In Package 2	1000
Package 2 Height	40.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.954 kg
Unit Type Of Package 3	P12
Number Of Units In Package 3	24000

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 3 Height	134.000 cm
Package 3 Width	80.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	101.500 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations