

# Product data sheet

Specifications

## Mureva FIX - installation tie - 194x9 mm - 100 pieces



ENN47942

### Main

Product Range	Mureva FIX
Product Type	Installation tie
Colour Tint	Black
Quantity Per Set	100 pieces

### Complementary

Minimum Tightening Diameter	10 mm
Maximum Tightening Diameter	42 mm
Resistance To Tearing	Resistance to tearing: 36 daN Ø 20 mm
Material	PA (polyamide) 12 Rislan®
Length	194 mm
Width	9 mm
Net Weight	0.003 kg

### Environment

Maximum Humidity Absorption	0.9 %
Operating Temperature	-60...85 °C 100 °C during 1000 hours 120 °C maximum
Flame Retardance	HB conforming to UL 94
Standards	EN 50146
Environmental Characteristic	UV resistant

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.5 cm
Package 1 Width	10.5 cm
Package 1 Length	20.5 cm
Package 1 Weight	3.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	100
Package 2 Height	8.5 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	10.5 cm
Package 2 Length	20.5 cm
Package 2 Weight	1.3 kg
Unit Type Of Package 3	CAR
Number Of Units In Package 3	2000
Package 3 Height	33.0 cm
Package 3 Width	35.0 cm
Package 3 Length	39.5 cm
Package 3 Weight	6.28 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information   Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations