



Main

Range	Asfora
Product or component type	Switch
Device presentation	Complete product
Load type	Load for energy saving lamps with ballast : 100 W
Colour tint	White
Type of packing	Flow-pack

Complementary

Switch function	1-pole
Number of rocker	1
Device mounting	Flush
Power range	2300 W
Rated current	10 AX 250 V AC
Marking	Without marking
Connections - terminals	Lift terminals
Number of cables	2 x 2.5 mm ²
Cable stiffness	Flexible Rigid Solid stranded
Wire stripping length	13 mm
Material	ABS (acrylonitrile butadiene-styrene)
Surface finish	Glossy
Conductor material	Copper
Fixing mode	Screws or claws 51...70 mm
Height	83 mm
Width	83 mm
Depth	43 mm
Projecting depth	15 mm
Product weight	0.0736 kg

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Quantity per set	Set of 1
------------------	----------

Environment

Standards	IEC 60669-1
Product certifications	VDE
Quality labels	CE
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------