


# Product data sheet

Specifications



## AsforaDIY - 1-pole switch - screwless terminals - cream - IP44

EPH0101223

 **Discontinued on:** Dec 15, 2022

 **Discontinued**

### Main

Range	Asfora
Product Or Component Type	Switch
Device Presentation	Complete product
Number Of Rocker	1
Switch Function	1-pole 1-way
Load Type	Load for energy saving lamps with ballast: 100 W
Colour Tint	Cream
Type Of Packing	Flow-pack with inlay card

### Complementary

Device Mounting	Flush
Power Range	2300 W
Rated Current	10 AX at 250 V AC
Number Of Cables	2 cable(s) 2.5 mm <sup>2</sup>
Cable Stiffness	Flexible Rigid Solid stranded
Wire Stripping Length	13.0 mm
Material	ABS (acrylonitrile butadiene-styrene)
Surface Finish	Glossy
Conductor Material	Copper
Fixing Mode	Screws or claws51...70 mm
Connections - Terminals	Screwless terminals
Width	83 mm
Height	83 mm
Depth	43.0 mm
Projecting Depth	15 mm
Net Weight	0.0846 kg

### Environment

Standards	IEC 60669-1
-----------	-------------

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	TSE VDE NF
Quality Labels	CE UKR
Ip Degree Of Protection	IP44
Ambient Air Temperature For Operation	-5...40 °C

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	8.300 cm
Package 1 Width	8.300 cm
Package 1 Length	4.300 cm
Package 1 Weight	95.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	9.400 cm
Package 2 Width	18.500 cm
Package 2 Length	27.500 cm
Package 2 Weight	734.000 kg
Unit Type Of Package 3	S04
Number Of Units In Package 3	96
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	12799.000 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency   RoHS/REACH

## Well-being performance

✓ Mercury Free

✓ Rohs Exemption Information   [Yes](#)

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	<a href="#">China RoHS declaration</a> Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Circularity Profile	No need of specific recycling operations