



Main

Range	Asfora
Product or component type	Push-button
Device presentation	Complete product
Colour tint	Cream
Type of packing	Flow-pack

Complementary

Switch function	1-pole push-button
Number of rocker	1
Device mounting	Flush
Power range	2300 W
Rated current	10 A 250 V AC
Marking	Bell symbol
Connections - terminals	Screwless terminals
Number of cables	2 x 2.5 mm ²
Cable stiffness	Flexible Rigid Solid stranded
Wire stripping length	13 mm
Material	ABS (acrylonitrile butadiene-styrene)
Surface finish	Glossy
Conductor material	Copper
Fixing mode	Screws or claws 51...70 mm
Height	83 mm
Width	83 mm
Depth	43 mm
Projecting depth	15 mm
Product weight	0.0705 kg

Quantity per set	Set of 1
------------------	----------

Environment

Standards	IEC 60669-1
Product certifications	NF TSE VDE
Quality labels	CE UKR
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------