



Main

Range	Asfora
Product or component type	Socket-outlet
Outlet standard description	Pin earth
Outlet poles configuration	2P + E
Device presentation	Complete product
Colour tint	Cream
Type of packing	Flow-pack with inlay card

Complementary

Socket number	1
Device mounting	Flush
Power range	3680 W
Rated current	16 A 250 V AC
Connections - terminals	Lift terminals
Number of cables	3 x 2.5 mm ²
Cable stiffness	Flexible Rigid Solid stranded
Wire stripping length	13 mm
Material	ABS (acrylonitrile butadiene-styrene) : cover frame ABS + PC : central plate
Surface finish	Glossy
Conductor material	Copper
Fixing mode	Screws or claws 51...69 mm
Height	83 mm
Width	83 mm
Depth	42 mm
Projecting depth	10 mm
Quantity per set	1

Product weight	0.081 kg
----------------	----------

Environment

Standards	IEC 60884-1
Product certifications	TSE SEP-BBJ
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1834 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months 18 months
-----------------	---------------------