

# Product data sheet

Specifications



## Asfora, TV-R-SAT intermediate socket, 8dB, cream

EPH3500323

⚠ Discontinued on: Jun 30, 2023

⚠ Discontinued

### Main

|                                      |                                 |
|--------------------------------------|---------------------------------|
| Range                                | Asfora                          |
| Product Or Component Type            | TV/SAT/R socket                 |
| Device Presentation                  | Complete product                |
| Tv Socket Type                       | Intermediate socket (passage)   |
| Wiring Device Additional Information | For series distribution systems |
| Type Of Packing                      | Flow-pack                       |

### Complementary

|                         |  |
|-------------------------|--|
| Device Mounting         | Flush  |
| Fixing Mode             | Claws51...80 mm  |
| Socket Number           | 3  |
| Tv Connector            | Male IEC 9.52 mm   |
| Radio Connector         | Female IEC 9.52 mm   |
| Sat Connector           | F type   |
| Attenuation             | 8 dB   |
| Colour Tint             | Cream  |
| Surface Finish          | Glossy   |
| Material                | ABS (acrylonitrile butadiene-styrene): central plate<br>ABS (acrylonitrile butadiene-styrene): cover frame |
| Dc Current Flow         | In SAT socket  |
| Number Per Line         | 4  |
| Connections - Terminals | Screwless terminals  |
| Conductor Material      | Copper   |
| Height                  | 83 mm  |
| Width                   | 83 mm  |
| Depth                   | 42 mm  |
| Projecting Depth        | 13 mm  |
| Net Weight              | 0.117 kg   |
| Ip Degree Of Protection | IP20   |

### Environment

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                |    |
|----------------|----|
| Quality Labels | CE |
|----------------|----|

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type Of Package 1       | PCE      |
| Number Of Units In Package 1 | 1        |
| Package 1 Height             | 11.0 cm  |
| Package 1 Width              | 16.0 cm  |
| Package 1 Length             | 5.0 cm   |
| Package 1 Weight             | 120.0 g  |
| Unit Type Of Package 2       | CAR      |
| Number Of Units In Package 2 | 10       |
| Package 2 Height             | 9.1 cm   |
| Package 2 Width              | 18.5 cm  |
| Package 2 Length             | 27.5 cm  |
| Package 2 Weight             | 1.339 kg |
| Unit Type Of Package 3       | S03      |
| Number Of Units In Package 3 | 60       |
| Package 3 Height             | 30.0 cm  |
| Package 3 Width              | 30.0 cm  |
| Package 3 Length             | 40.0 cm  |
| Package 3 Weight             | 8.409 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|

## Sustainability

**Green Premium™** label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

|                       |   |     |
|-----------------------|---|-----|
| ✓                     | Reach Free Of Svhc  |     |
| ✓                     | Toxic Heavy Metal Free  |     |
| ✓                     | Mercury Free  |     |
| ✓                     | Rohs Exemption Information  | Yes |
|                       |   |     |
| Reach Regulation      | REACH Declaration   |     |
| Eu Rohs Directive     | Compliant<br>EU RoHS Declaration  |     |
| China Rohs Regulation | China RoHS declaration<br>Pro-active China RoHS declaration (out of China RoHS legal scope)                                 |     |
| Weee                  | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins |     |
| Circularity Profile   | No need of specific recycling operations  |     |