



Main

Range	Asfora
Product or component type	Card switch
Device presentation	Without frame
Provided equipment	Without relay unit
Colour tint	Bronze
Type of packing	Flow-pack

Complementary

Local signalling	LED
Device mounting	Flush
Power range	2300 W
Rated current	10 A 250 V AC
Marking	Without marking
Connections - terminals	Screwless terminals
Number of cables	2 x 2.5 mm ²
Cable stiffness	Flexible Rigid Solid stranded
Wire stripping length	13 mm
Material	ABS (acrylonitrile butadiene-styrene)
Surface finish	Painted
Conductor material	Copper
Fixing mode	Screws or claws 51...70 mm
Height	71 mm
Width	71 mm
Depth	53 mm
Projecting depth	23 mm
Product weight	0.0738 kg

Quantity per set	Set of 1
------------------	----------

Environment

Product certifications	TSE VDE
Quality labels	CE UKR
IP degree of protection	IP20

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1809 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations