

Product data sheet

Specifications



Ultra - installation trunking - 151 x 50 mm - plastic - white - 2 m

ETK151502

Main

Range	Ultra
Product Or Component Type	Installation trunking
Device Application	Cable distribution
Colour Tint	White (RAL 9010)
Quantity Per Set	8 m
Type Of Packing	Protective foil

Complementary

Compartment Partitioning	1 compartment
Trunking Dimension	151 x 50 mm
Device Composition	Trunking base
Trunking Material	Plastic
Front Opening Size	120 mm
Fixing Mode	Screw-fixed Pre-punched fixing hole 230 mm
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	151 mm
Width	50 mm

Environment

Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Standards	EN 50085-1:2005 EN 50085-2-1:2006

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	5 cm
Package 1 Width	15.1 cm
Package 1 Length	200 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Weight	2.25 kg
Unit Type Of Package 2	BB1
Number Of Units In Package 2	8
Package 2 Height	11.5 cm
Package 2 Width	18 cm
Package 2 Length	204 cm
Package 2 Weight	9.1 kg
Unit Type Of Package 3	PAL
Number Of Units In Package 3	240
Package 3 Height	72.5 cm
Package 3 Width	205 cm
Package 3 Length	120 cm
Package 3 Weight	273 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations