


Product data sheet

Specifications



Ultra - branching piece - 101 x 50 mm to 151 x 50 mm - ABS - white

ETK15154

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Ultra
Product Or Component Type	Reducer
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 5

Complementary

Trunking Dimension	101 x 50 mm 151 x 50 mm
Trunking Material	Plastic
Fixing Mode	Snap-fitted
Material	PC/ABS
Height	155 mm
Width	66 mm
Depth	52 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Ambient Air Temperature For Operation	-25...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	15.5 cm
Package 1 Width	6.6 cm
Package 1 Length	5.2 cm
Package 1 Weight	52.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Weight	260 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	CAR
Number Of Units In Package 3	35
Package 3 Weight	1.82 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACH Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations