



Main

Product or component type	Mini trunking
Device application	Cable distribution
Colour tint	White RAL 9010
Quantity per set	156 m

Complementary

Trunking material	Plastic
Compartment partitioning	1 compartment
Trunking dimension	16 x 16 mm
Fixing mode	Power cable : screw-fixed Low voltage cable : adhesive tape Pre-punched fixing hole with distance of 230 mm between centers
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	16 mm
Width	16 mm

Environment

IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-5...60 °C
Environmental health and issues	Cadmium free Lead free
Product certifications	Low voltage directive 2006/95/EC
Standards	EN 50085-1 : 2005 EN 50085-2-1 : 2006

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1826 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product environmental profile	Available Product Environmental Profile
Product end of life instructions	Need no specific recycling operations