

Product data sheet

Specifications

Ultra - mini trunking - 16 x 16 mm - PVC - white - 3 m



ETK16816

 **Discontinued on:** Oct 9, 2019

 **Discontinued**

Main

Range	Ultra
Product Or Component Type	Mini trunking
Device Application	Cable distribution
Type Of Packing	Plastic bag
Quantity Per Set	Set of 45

Complementary

Trunking Material	Plastic
Compartment Partitioning	1 compartment
Trunking Dimension	16 x 16 mm
Fixing Mode	Pre-punched fixing hole 230 mm Power cable: screw-fixed Low voltage cable: adhesive tape
Material	PVC (polyvinyl chloride)
Length	3000 mm
Height	16 mm
Width	16 mm

Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-5...60 °C
Standards	EN 50085-1:2005 EN 50085-2-1:2006

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	1.7 cm
Package 1 Width	1.6 cm
Package 1 Length	300 cm
Package 1 Weight	350 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Circularity Profile

No need of specific recycling operations