

Product data sheet

Specifications



Ultra - adjustable internal corner . 21 x 12 mm - ABS - white

ETK20520

 **Discontinued on:** Jun 30, 2023

 **Discontinued**

Main

Range Of Product	Ultra
Product Or Component Type	Internal corner
Device Application	Cable distribution
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 20
Market Segment	Residential Small commercial

Complementary

Trunking Dimension	21 x 12 mm
Trunking Material	Plastic
Adjustment	Adjustable
Fixing Mode	Snap-fitted
Material	ABS thermoplastic enclosure
Height	22.8 mm
Width	41.5 mm
Depth	41.5 mm

Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.000 cm
Package 1 Width	2.500 cm
Package 1 Length	5.000 cm
Package 1 Weight	5.600 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 2	BB1
Number Of Units In Package 2	20
Package 2 Height	9.000 cm
Package 2 Width	11.000 cm
Package 2 Length	13.500 cm
Package 2 Weight	150.000 g
Unit Type Of Package 3	S04
Number Of Units In Package 3	720
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	5.991 kg

Contractual warranty

Warranty	18 months
----------	-----------

Sustainability

Green Premium™ label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation

[REACH Declaration](#)

Eu Rohs Directive

Pro-active compliance (Product out of EU RoHS legal scope)

[EU RoHS Declaration](#)

China Rohs Regulation

[China RoHS declaration](#)

Pro-active China RoHS declaration (out of China RoHS legal scope)

Circularity Profile

No need of specific recycling operations