

# Product data sheet

Specifications



## Ultra - socket outlet - single - pin earth - white

ETK21046EW

### Main

Product Or Component Type	Socket-outlet
Colour Tint	White
Quantity Per Set	Set of 10

### Complementary

Ground Lug Position	90° ground lug
[In] Rated Current	16 A
[Ue] Rated Operational Voltage	250 V AC
Number Of Power Socket Outlets	1 pin earth - shuttered
Fixing Mode	Snap-fitted
Material	PC/ABS
Height	45 mm
Width	45 mm
Depth	41 mm

### Environment

Ip Degree Of Protection	IP40
Ambient Air Temperature For Operation	-5...60 °C

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	4.000 cm
Package 1 Width	4.500 cm
Package 1 Length	4.500 cm
Package 1 Weight	44.000 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	10
Package 2 Height	4.500 cm
Package 2 Width	10.000 cm
Package 2 Length	23.000 cm
Package 2 Weight	487.000 g

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 3	S04
Number Of Units In Package 3	280
Package 3 Height	30.000 cm
Package 3 Width	40.000 cm
Package 3 Length	60.000 cm
Package 3 Weight	14.017 kg

## Contractual warranty

Warranty	18 months
----------	-----------

# Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

Eu Rohs Directive	Not applicable, out of EU RoHS legal scope
Circularity Profile	No need of specific recycling operations