

# Product data sheet

Specifications

## Ultra - mini trunking - 25 x 25 mm - PVC - white - 2 m



ETK25325

### Main

Range	Ultra
Product Or Component Type	Mini trunking
Device Application	Cable distribution
Quantity Per Set	Set of 32
Market Segment	Residential Small commercial

### Complementary

Trunking Material	Plastic
Compartment Partitioning	1 compartment
Trunking Dimension	25 x 25 mm
Fixing Mode	Pre-punched fixing hole 230 mm Power cable: screw-fixed
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	25 mm
Width	25 mm

### Environment

Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07
Ambient Air Temperature For Operation	-5...60 °C
Standards	EN 50085-1:2005 EN 50085-2-1:2006

### Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.5 cm
Package 1 Width	2.5 cm
Package 1 Length	210.0 cm
Package 1 Weight	362.5 g
Unit Type Of Package 2	CAR

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 2	64
Package 2 Height	11.5 cm
Package 2 Width	22.5 cm
Package 2 Length	211.0 cm
Package 2 Weight	11.619 kg

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations