

# Product data sheet

Specifications

Ultra - bend 90° - 25 x 16/25 mm -  
ABS - white - DIY - 2 pack



ETK25341D

## Main

Range Of Product	Ultra
Product Or Component Type	90° bend
Device Application	Cable distribution
Colour Tint	White (RAL 9010)
Quantity Per Set	Set of 2

## Complementary

Trunking Dimension	25 x 16 mm 25 x 25 mm
Trunking Material	Plastic
Fixing Mode	Snap-fitted
Material	ABS thermoplastic enclosure
Height	27 mm
Width	45 mm
Depth	45 mm

## Environment

Standards	EN 50085-1:2005 EN 50085-2-1:2006
Ambient Air Temperature For Operation	-5...60 °C
Ip Degree Of Protection	IP40
Ik Degree Of Protection	IK07

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	2.7 cm
Package 1 Width	4.5 cm
Package 1 Length	4.5 cm
Package 1 Weight	6.0 g
Unit Type Of Package 2	BB1
Number Of Units In Package 2	5
Package 2 Height	6.0 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Width	8.0 cm
Package 2 Length	20.0 cm
Package 2 Weight	42.0 g

## Sustainability

**Green Premium™ label** is Schneider Electric’s commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product’s sustainability >](#)



RoHS/REACH

## Well-being performance

✓ Reach Free Of Svhc

✓ Toxic Heavy Metal Free

✓ Mercury Free

✓ Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation	<a href="#">REACH Declaration</a>
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Circularity Profile	No need of specific recycling operations