



Main

Range of product	Ultra
Product or component type	Lid infill
Type of floor	In-cavity floor Raised floor Screeded floor
Floor box shape	Rectangular
Colour tint	Grey RAL 7011
Quantity per set	Set of 1

Complementary

Fixing mode	Snap-fitted
Number of modules	6 modules
Material	PA (polyamide) 6 GF10
Height	4 mm
Width	195 mm
Depth	148 mm

Environment

Environmental health and issues	Halogen free
Standards	IEC 60670-1 UNE 20451
Ambient air temperature for operation	-5...60 °C
IP degree of protection	IP20

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 1642 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------
