



### Main

Product or component type	Mini trunking
Device application	Wiring device adaptation
Colour tint	White (RAL 9010)
Quantity per set	40 m
Market segment	Residential Small commercial

### Complementary

Trunking material	Plastic
Compartment partitioning	3 compartments
Trunking dimension	60 x 21 mm
Fixing mode	Pre-punched fixing hole 230 mm Power cable: screw-fixed
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	60 mm
Width	21 mm

### Environment

IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-5...60 °C
Environmental health and issues	Cadmium free Lead free
Standards	EN 50085-1:2005 EN 50085-2-1:2006

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS declaration</a> Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------