



### Main

Product or component type	Mini trunking
Device application	Wiring device adaptation
Colour tint	White RAL 9010
Quantity per set	24 m

### Complementary

Trunking material	Plastic
Compartment partitioning	3 compartments
Trunking dimension	74 x 21 mm
Fixing mode	Power cable : screw-fixed Pre-punched fixing hole with distance of 230 mm between centers
Material	PVC (polyvinyl chloride)
Length	2000 mm
Height	74 mm
Width	21 mm

### Environment

IP degree of protection	IP40
IK degree of protection	IK07
Ambient air temperature for operation	-5...60 °C
Environmental health and issues	Cadmium free Lead free
Standards	EN 50085-1 : 2005 EN 50085-2-1 : 2006

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1826 - Schneider Electric declaration of conformity

[Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available <a href="#">Product Environmental Profile</a>
Product end of life instructions	Need no specific recycling operations

**Contractual warranty**

Warranty period	18 months
-----------------	-----------