

# Product data sheet

Specifications



## Electronic VAR control 60 amp 380-480 VAC N12 Enclosure

EVCP060D5N12

 To be discontinued on: Jun 30, 2024

 To be discontinued

### Main

Range Of Product	AccuSine
Product Name	AccuSine PFV+
Product Or Component Type	Electronic VAR controller

### Complementary

Network Type	3P
Network Configuration	3 or 4 wires
Network Rated Voltage	380...480 V AC
Network Frequency	50/60 Hz +/- 3 % auto-sensing
Maximum Permissible Voltage	1.1 x Un
Rms Output Current Rating	60 A
Reactive Power Rating	50 kvar 480 V AC 50/60 Hz
Operating Mode	Mains current balancing Power factor correction Volt-var support
Installation Location	Indoor
Enclosure Mounting	Floor-standing
Protection Type	Circuit breaker protection
Disconnect Type	Door-interlocked with rotary handle
Interrupt Capacity	200 kA
Heat Dissipation	Rear plenum with forced ventilation for high heat flow
Electromagnetic Compatibility	Conducted EMC, class A conforming to EN 61000-6-4
Accessibility For Operation	Front
Location Of Connection	Top or bottom

### Environment

Enclosure Degree Of Protection	UL type 12
Environmental Characteristic	Operating: 3C2 conforming to IEC 60721-3-3 Operating: 3S2 conforming to IEC 60721-3-3 Storage: 3C3 conforming to IEC 60721-3-3 Storage: 3S3 conforming to IEC 60721-3-3
Operating Altitude	<= 1000 m 1 % per 100 m

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Air Temperature For Operation	0...40 °C 0...50 °C maximum with current derating of 2 % per °C
Relative Humidity	0...95 %
Pcba Protection	Conformal coated
Standards	EN 61000-6-4 CSA C22.2 No 14 EN 60439-1 UL 508 CSA C22.2 No 60947-1-07 UL 60947-1
Product Certifications	RCM CE cULus ABS
Ambient Air Temperature For Storage	-20...60 °C
Height	2100 mm
Width	800 mm
Depth	500 mm
Colour	Light grey (RAL 7035)

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	233.1 cm
Package 1 Width	119.4 cm
Package 1 Length	119.4 cm
Package 1 Weight	381.0 kg

## Contractual warranty

Warranty	18 months
----------	-----------

## Sustainability




**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)

## Well-being performance

	Toxic Heavy Metal Free	
	Mercury Free	
	Rohs Exemption Information	Yes
Eu Rohs Directive	Compliant	<a href="#">EU RoHS Declaration</a>
China Rohs Regulation	<a href="#">China RoHS declaration</a>	Product out of China RoHS scope. Substance declaration for your information
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>	