



Purchase

APC
 G35TEFBAT10K40H

Overview

Description	MGE Galaxy 3500 empty battery frame for use with non-modular third party batteries only.
Model Name	MGE Galaxy 3500 Empty Frame for Batteries 10-40kVA 400V Floormount
Includes	Installation guide
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Andorra

Input

Nominal Input Voltage	400V 3PH
Input Frequency	50/60 Hz

Batteries & Runtime

Battery Type	No internal battery - uses external battery system
Battery mounting	Enclosed battery cabinet
Battery Placement	External Frame

Physical

Net Weight	147 kg
Maximum Height	1490 mm
Maximum Width	523 mm
Maximum Depth	834 mm
Shipping Weight	294 kg
Shipping Width	724 mm
Shipping Height	1664 mm
Shipping Depth	1105 mm
Color	Grey

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 85 %
Operating Elevation	0-3000 meters
Storage Temperature	0 - 30 °C
Storage Relative Humidity	0 - 85 %
Storage Elevation	0-4500 meters

Conformance

Approvals	EN 50091-2
Standard warranty	1 year repair or replace