



Purchase

APC
 G35TOPT006

Overview

Model Name	MGE Galaxy 3500 Baying Kit, XR to XR
Includes	Installation guide , Mounting Hardware
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Andorra , United Arab Emirates , Afghanistan , Antigua And Barbuda , Anguilla , Albania , Armenia , Netherlands Antilles , Angola , Argentina , Austria , Australia , Aruba , Azerbaijan , Bosnia And Herzegovina , Barbados , Bangladesh , Belgium , Burkina Faso , Bulgaria , Bahrain , Burundi , Benin , Bermuda , Brunei Darussalam , Bolivia , Brazil , Bahamas , Bhutan , Botswana , Belarus , Belize , Canada , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Central African Republic , Congo , Switzerland , Cote D'Ivoire , Cook Islands , Chile , Cameroon , China , Colombia , Costa Rica , Serbia And Montenegro , Cuba , Cyprus , Czech Republic , Germany , Djibouti , Denmark , Dominica , Dominican Republic , Algeria , Ecuador , Estonia , Egypt , Western Sahara , Spain , Ethiopia , Finland , Fiji , Falkland Islands (Malvinas) , France , Gabon , United Kingdom , Grenada , Georgia , French Guiana , Ghana , Gibraltar , Gambia , Guinea , Guadeloupe , Equatorial Guinea , Greece , Guatemala , Guyana , Hong Kong , Honduras , Croatia , Haiti , Hungary , Indonesia , Ireland , Israel , India , Iraq , Iran (Islamic Republic Of) , Iceland , Italy , Jamaica , Jordan , Kenya , Cambodia , SAINT KITTS AND NEVIS , KOREA, REPUBLIC OF , Kuwait , Cayman Islands , Kazakhstan , Lebanon , SAINT LUCIA , Liechtenstein , Sri Lanka , Liberia , Lesotho , Lithuania , Luxembourg , Latvia , Morocco , Moldova, Republic Of , Madagascar , Macedonia , Mali , Myanmar , Martinique , Mauritania , Malta , Mauritius , Malawi , Mexico , Malaysia , Mozambique , Namibia , Niger , Nigeria , Nicaragua , Netherlands , Norway , Nepal , New Zealand , Oman , Panama , Peru , Papua New Guinea , Philippines , Pakistan , Poland , Puerto Rico , Portugal , Paraguay , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Sudan , Sweden , Singapore , Slovenia , Slovakia (Slovak Republic) , Sierra Leone , Senegal , Somalia , El Salvador , Turks And Caicos Islands , Chad , Togo , Thailand , Turkmenistan , Tunisia , East Timor , Turkey , Trinidad And Tobago , Taiwan , TANZANIA, UNITED REPUBLIC OF , Ukraine , Uganda , United States , Uruguay , Uzbekistan , SAINT VINCENT AND THE GRENADINES , Venezuela , VIRGIN ISLANDS (UNITED STATES) , Viet Nam , Yemen , Mayotte , South Africa , Zambia , Zimbabwe

Physical

Net Weight	11.36 kg
Maximum Height	25 mm
Maximum Width	1357 mm
Maximum Depth	232 mm
Shipping Weight	13.64 kg

Shipping Height	55 mm
Shipping Width	1375 mm
Shipping Depth	270 mm

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-999.9 meters
Storage Temperature	0 - 40 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-999.9 meters

Conformance

Standard warranty	1 year repair or replace
-------------------	--------------------------