

Product data sheet

Characteristics

G35TOPT007

MGE Galaxy 3500 Seismic Kit, 14inch/351mm (Narrow)



Purchase

APC
[G35TOPT007](#)

Overview

Model Name	MGE Galaxy 3500 Seismic Kit, 14inch/351mm (Narrow)
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Andorra , United Arab Emirates , Albania , Armenia , Angola , Austria , Azerbaijan , Bosnia And Herzegovina , Belgium , Burkina Faso , Bulgaria , Bahrain , Burundi , Benin , Botswana , Belarus , Canada , CONGO, THE DEMOCRATIC REPUBLIC OF THE , Central African Republic , Congo , Switzerland , Cote D'Ivoire , Cameroon , Serbia And Montenegro , Cyprus , Czech Republic , Germany , Djibouti , Denmark , Algeria , Estonia , Egypt , Western Sahara , Spain , Ethiopia , Finland , France , Gabon , United Kingdom , Georgia , French Guiana , Ghana , Gibraltar , Gambia , Guinea , Guadeloupe , Equatorial Guinea , Greece , Croatia , Hungary , Ireland , Israel , Iraq , Iran (Islamic Republic Of) , Iceland , Italy , Jordan , Kenya , Kuwait , Kazakhstan , Lebanon , Liechtenstein , Liberia , Lesotho , Lithuania , Luxembourg , Latvia , Morocco , Moldova , Republic Of , Madagascar , Macedonia , Mali , Martinique , Mauritania , Malta , Mauritius , Malawi , Mozambique , Namibia , Niger , Nigeria , Netherlands , Norway , Oman , Pakistan , Poland , Portugal , Qatar , Reunion , Romania , Russian Federation , Rwanda , Saudi Arabia , Sudan , Sweden , Slovenia , Slovakia (Slovak Republic) , Sierra Leone , Senegal , Somalia , Turks And Caicos Islands , Chad , Togo , Turkmenistan , Tunisia , Turkey , TANZANIA, UNITED REPUBLIC OF , Ukraine , Uganda , United States , Uzbekistan , Yemen , Mayotte , South Africa , Zambia , Zimbabwe

Physical

Net Weight	11.36 kg
Maximum Height	25 mm
Maximum Width	1357 mm
Maximum Depth	232 mm
Shipping Weight	13.64 kg
Shipping Height	55 mm
Shipping Width	1375 mm
Shipping Depth	11 mm

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %

Operating Elevation	0-999.9 meters
Storage Temperature	0 - 40 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-999.9 meters

Conformance

Standard warranty	1 year repair or replace
-------------------	--------------------------