



### Purchase

APC  
 G35TSBPAR20K30F

### Overview

Model Name	MGE Galaxy 3500 Parallel Maintenance Bypass, up to 3 units 20-30kVA 208V Floormount
Includes	Installation guide
Standard Lead Time	Usually Ships within 2 Weeks
Product Distribution	Anguilla

### Output

Nominal Output Voltage	208V 3PH
------------------------	----------

### Input

Nominal Input Voltage	208V 3PH
Input Frequency	60 Hz

### Physical

Net Weight	144.09 kg
Maximum Height	1487 mm
Maximum Width	351 mm
Maximum Depth	837 mm
Shipping Weight	205 kg
Shipping Height	1664 mm
Shipping Width	724 mm
Shipping Depth	1105 mm

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters

---

Storage Temperature	0 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-9000 meters

---

**Conformance**

---

Approvals	CSA
Standard warranty	1 year repair or replace

---