



Main

Range compatibility	Lexium 32
Product or component type	Planetary gearbox
Gear box type	Straight teeth
Device short name	GBX
Gearbox external diameter	40 mm
Product compatibility	BSH0704...
Reduction ratio	9:1

Complementary

Torsional backlash	< 28 arc.min
Torsional rigidity	1.1 N.m/arcmin
Housing colour	Black
Housing material	Black anodized aluminium
Shaft material	C 45
Additional information	Lubricated for life
Service life in hours	At 100 rpm at 30 °C
Efficiency	94 %
Maximum radial force Fr	160 N at 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 °C 200 N at 100 rpm, force applied at mid-distance from output shaft during 10000 hour at 30 °C
Maximum axial force Fa	160 N at 100 rpm, during 30000 hour at 30°C 200 N at 100 rpm, during 10000 hour at 30°C
Maximum output torque	26 N.m at 100 rpm at 30 °C
Product weight	0.45 kg

Environment

Noise level	55 dB at 1 m, no-load
IP degree of protection	IP54 on shaft output
Ambient temperature for operation	-25...90 °C

Contractual warranty

Warranty period	18 months
-----------------	-----------