

# Product data sheet

Specifications



gearbox with straight teeth GBX- Ø 60 mm- reduction 8:1- < 16arcmin- 18 N.m

GBX0600080573G

⚠ Discontinued

## Main

Range Compatibility	Lexium 05
Product Or Component Type	Planetary gearbox
Gear Box Type	Straight teeth
Device Short Name	GBX
Gearbox External Diameter	60 mm
Product Compatibility	BRH0573
Reduction Ratio	8:1

## Complementary

Maximum Torsional Backlash	16 arc.min
Torsional Rigidity	2.3 N.m/arcmin
Housing Colour	Black
Housing Material	Black anodized aluminium
Shaft Material	C 45
Additional Information	Lubricated for life
Service Life In Hours	30000 h at 100 rpm at 30 °C
Efficiency	96 %
Mounting Position	Any position
Maximum Radial Force Fr	340 N at 100 rpm, force applied at mid-distance from output shaft during 30000 hour at 30 °C 500 N at 100 rpm, force applied at mid-distance from output shaft during 10000 hour at 30 °C
Maximum Axial Force Fa	450 N at 100 rpm, during 30000 hour at 30°C 600 N at 100 rpm, during 10000 hour at 30°C
Moment Of Inertia	0.065 g.cm²
Continuous Output Torque	18 N.m at 100 rpm at 30 °C
Maximum Output Torque	29 N.m at 100 rpm at 30 °C
Net Weight	0.9 kg

## Environment

Noise Level	58 dB at 1 m, no-load
Ip Degree Of Protection	Shaft output: IP54

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Ambient Temperature For Operation	-25...90 °C
--------------------------------------	-------------

## Contractual warranty

Warranty	18 months
----------	-----------