



## Main

Range	Ultimate
Product or component type	Switched socket with USB charger
Device presentation	Complete product
Colour tint	Black front plate
Surface finish	Stainless steel
Connections - terminals	Screw terminals
Switch function	1-pole

## Complementary

Device mounting	Flush Surface
Integrated connection type	USB port 2 5 V DC 2.1 A Socket-outlet 2 250 V AC 13 A 50/60 Hz
Actuator	Rocker
Number of gangs	2 gangs
Pilot light	Without LED
Fixing mode	By screws M3.5 2 26 mm By screws M3.5 2 32 mm
Clamping connection capacity	2 x 6 mm <sup>2</sup> solid 3 x 4 mm <sup>2</sup> solid 5 x 2.5 mm <sup>2</sup> solid 3 x 4 mm <sup>2</sup> stranded 5 x 2.5 mm <sup>2</sup> stranded
Material	Steel
Product compatibility	Mobile/Tablet Apple Mobile/Tablet Samsung Mobile/Tablet LG Mobile/Tablet Blackberry Mobile/Tablet HTC Mobile/Tablet Sony Mobile/Tablet Huawei Technologies

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Directives	2004/108/EC - electromagnetic compatibility 2006/95/EC - low voltage directive
Quality labels	CE
Quantity per set	Set of 1
Type of packing	Bag
Type of installation	Indoor
Depth	5.5 mm
Width	148 mm
Height	87.7 mm

## Environment

IP degree of protection	IP20
Standards	BS 1363-2

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1642 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations